

**GWX angle grinder, Type: 9-125S****Order data**

Order number	077050 9-125S
GTIN	3165140962568
Item class	03C

**Description****Version:**

- **Quick and easy:** Easy change of angle grinder accessories without any parts that could be lost or need for additional tools.
- **No additional wrenches required.**
- **Comprehensive:** Huge range of angle grinders and accessories with complete backwards compatibility.
- **Maximum convenience** due to 100% quick tool exchange requiring no tools.
- **Reliable:** Directional accessories can no longer be mounted incorrectly thanks to the innovative X-LOCK system. Very high user protection thanks to the acoustic signal when fitting is correct.
- **Clean working without annoying scratches!** Less prominent and fewer scuffs with X-LOCK angle grinders.

125-mm angle grinder with 900 W motor. **X-Lock system.**

**Supplied with:**

Including additional handle, safety guard and package.

**Technical description**

Power supply	Mains-powered
Special features	Variable speed
Speed range	2800 - 11000 min <sup>-1</sup>
maximum disc Ø	125 mm

Restart block	yes
Mains frequency	50 Hz
Series	X-LOCK system
AC supply voltage	230 V
Power consumption	900 W
Manufacturer's designation	GWX 9-125S
Weight	2.1 kg
Type of product	Angle grinder

---

## Accessories

GWX angle grinderwithout battery Type 18V15SC	077011 18V15SC
GWX angle grinder Type 9-115S	077050 9-115S
GWX angle grinderwithout battery Type 18V15C	077011 18V15C
GWX angle grinder Type 19-125S	077050 19-125S
GWX angle grinder Type 14-125	077050 14-125