

**Shim stock 150×2500 mm, Brass, Thickness: 0,09mm****Order data**

Order number	478740 0,09
GTIN	4067263105305
Item class	42H

**Description****Version:**

This precision gauging shim is provided on rolls in plastic boxes (easy to pull off). The individual boxes can be stacked in a block, saving space and protecting the material from dirt.

**Brass** material No. CuZn 37 (CW508L), hard rolled, bright surface.

**Application:**

**Setting** tools; **adjusting** devices; **balancing** tolerances; **shimming** components; **aligning** machines; **setting up** forms; **adjusting** bearing play; **adjusting** drive alignments; **setting** shear knives; **aligning** components etc.

**Technical description**

Error limit	±4 µm
Thickness	0.09 mm
Material	Brass
Film length	2500 mm
Film width	150 mm
Product name attribute	Brass
Type of product	Shim stock

