



Shim stock 150×2500 mm, stainless steel, Thickness: 0,7mm



Order data

| | |
|--------------|---------------|
| Order number | 478720 0,7 |
| GTIN | 4067263105466 |
| Item class | 42H |

Description

Version:

This precision gauging shim is provided on rolls in plastic boxes (easy to pull off). The individual boxes can be stacked in a block, saving space and protecting the material from dirt.

Stainless and acid resistant steel, material No. 1.4301, cold rolled, spring hardened, bright surface.

Application:

Setting tools; **adjusting** devices; **balancing** tolerances; **shimming** components; **aligning** machines; **setting up** forms; **adjusting** bearing play; **adjusting** drive alignments; **setting** shear knives; **aligning** components etc.

Technical description

| | |
|------------------------|--|
| Error limit | ±12 µm |
| Thickness | 0.7 mm |
| Material | non-rusting and acid resistant stainless steel |
| Film length | 2500 mm |
| Film width | 150 mm |
| Product name attribute | stainless steel |

Type of product

Shim stock