



## Shim stock 150×2500 mm, stainless steel, Thickness: 0,03mm



### Order data

Order number	478720 0,03
GTIN	4067263105343
Item class	42H

### Description

#### Version:

This precision gauging shim is provided on rolls in plastic boxes (easy to pull off). The individual boxes can be stacked in a block, saving space and protecting the material from dirt.

**Stainless** and acid resistant steel, material No. 1.4301, cold rolled, spring hardened, bright surface.

#### Application:

**Setting** tools; **adjusting** devices; **balancing** tolerances; **shimming** components; **aligning** machines; **setting up** forms; **adjusting** bearing play; **adjusting** drive alignments; **setting** shear knives; **aligning** components etc.

### Technical description

Error limit	±2 µm
Material	non-rusting and acid resistant stainless steel
Thickness	0.03 mm
Film length	2500 mm
Film width	150 mm
Product name attribute	stainless steel

Type of product

Shim stock