



LED headlamp with rechargeable battery, Type: HF8R-WORK



Order data

Order number	081391 HF8R-WORK
GTIN	4058205031967
Item class	04B

Description

Version:

Powerful high-performance LED headlamps for professional use.

- **Pivoting head and stepless focussing function.**
- **Intuitive operation and stepless dimming.**
- **Exchangeable and washable head band.**
- **Ledlenser connecting system as a standardised interface permits easy connection with a comprehensive range of accessories.**

Function:

IP68: Protected against continuous submersion in water (watertight) and protected against penetration by dust (dust-tight), also completely protected against touching.

Technical description

Battery voltage	3.7 V
Battery capacity	3.7 Ah
Illumination step 2	20 lm
Illumination range	210 m
Number of rechargeable batteries contained	1
Illumination time	3 - 10 h

Advanced Focus System (AFS)	yes
Illumination time stage 2	90 h
Weight	198 g
Dimmable lighting	yes
Colour of housing	black
Type of rechargeable battery	Lithium-ion
Power supply	Mains operated
Manufacturer's designation	HF8R WORK
rechargeable	yes
IP Index of Protection	IP 68
Illumination	300 - 900 lm
Light current boost	1600 lm
Type of product	Headlamp