

Mahr

External micrometer – SPECIAL OFFER, Measuring range: 0-25mm



Order data

Order number	400410 0-25
GTIN	4059192003647
Item class	43A

Description

Version:

Precision lapped, carbide-tipped measuring faces.

Hardened and ground measuring spindle.

Locking by clamping lever.

With ratchet and hand temperature protection.

With clearly engraved, black divisions and numerals.

Supplied with:

From size 25-50 including 1 setting standard.

Technical description

Barrel Ø	17.5 mm
Spindle Ø	6.5 mm
Error limit	4 µm
Standard	DIN 863
Micrometer barrel graduations	1/50 mm
Scale divisions	0.01 mm
Calibration	B1
Measuring range	0 - 25 mm
Measurement technology	analogue

Packaging

sturdy box

Type of product

External tube micrometer

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/400410-0-25>