

**Internal micrometer set – SPECIAL OFFER, Measuring range: 6-12mm****Order data**

Order number	408910 6-12
GTIN	4059192010799
Item class	43A

Description**Version:**

Satin chrome-plated scales and operating parts. Measuring spindle through hardened and ground. Quick drive with integral clutch. Self-centring micrometer head from 12 mm with carbide measuring jaws. From 12 mm **for measuring down to the bottom of the hole**. From 40 mm the micrometer head is of aluminium, to save weight.

Supplied with:

Internal micrometers No. 428900 with appropriate setting rings.

Technical description

Number of micrometers	3
Number of setting rings	2
Setting ring Ø	8 / 10 mm
Measuring range	6 - 12 mm
Scale divisions	0.001 mm
Standard	DIN 863
Micrometer barrel graduations	1/50 mm

Measurement technology	analogue
Packaging	sturdy box
Calibration	S6
Type of product	3-point internal micrometer

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/408910-6-12>