

HEDI**Cable drum plastic for F, B, PL and CZ, Type: 25V****Order data**

Order number	081127 25V
GTIN	4003644015351
Item class	08B

Description**Version:**

Hedi® cable drums stand for “Made in Germany” quality and a long service life. The drum body is specially designed to optimally guide the cable. The integrated rotation stop switch prevents accidental drum rotation. All cable drums are equipped with thermal cut-out switches.

· Overheating protection.

For use in dry environments.

Function:

IP20: Protected against penetration by foreign bodies with $\varnothing < 12$ mm, however touching should be avoided, and offers no protection against water.

IP Index of Protection: IP 20

Rated power unrolled: 3500 (16 A) W

Cable class: H05VV-F

Cable structure: 3G1.5

Material cable: PVC red

Cable length: 25 m

Number of sockets: 4

Technical description

Rated power unrolled	3500 (16 A) W
Cable length	25 m
AC supply voltage	250 V
Cable class	H05VV-F
Cable structure	3G1.5
Type	25V
Material cable	PVC red
IP Index of Protection	IP 20
Material of body	Plastic
Number of sockets	4
Power supply	Mains operated
Diagnostic system present	no
Type of product	Cable drum