



Digital groove depth gauge IP 67, Measuring range: 200mm

Order data

Order number	418758 200
GTIN	4059192066123
Item class	43A

Description

Version:

For measuring cut-outs, grooves, recesses, shoulders etc. The REFERENCE measuring system saves and retains the set zero position, even after being switched on again. The lock function prevents measurement errors arising from accidentally touching the control buttons. Measuring beam with double hook. Both contact faces in a single plane.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

1 battery No. 081560 size CR2032.

Optional extras:

Data cable No. 498940.

Technical description

Calibration	A2
Article no of the battery / rechargeable battery fitted	081560 CR2032
Reversible reading	0.01 mm
Reversible reading	mm / inch
Bridge length	100 mm
Cross-section measuring beam	12 × 3.5 mm
Reversible reading	0.0005 in
Measuring range	0 - 200 mm
Power supply	Battery-powered

IP Index of Protection	IP 67
Measurement deviation E MPE	± 0.03 mm
Number of batteries contained	1
Standard	ISO 13385
Interface	USB interface
Interface	USB interface
Interface	Digimatic interface
Measured value saving	MAHR reference-lock system
Measurement technology	digital
Material	Stainless steel, INOX
Packaging	Wallet
Type of product	Groove depth gauge

Services

DAkKS calibration Vernier hook depth gauge maximum measuring range 200 mm	021230 200
Calibration Vernier hook depth gauge maximum measuring range 200 mm	021220 200

Accessories

Button cell / special battery Battery type CR2032	081560 CR2032
Battery compartment cover	412235