



Digital groove depth gauge IP 67, Measuring range: 300mm



Order data

Order number	418758 300
GTIN	4059192066130
Item class	43A

Description

Version:

For measuring cut-outs, grooves, recesses, shoulders etc. The REFERENCE measuring system saves and retains the set zero position, even after being switched on again. The lock function prevents measurement errors arising from accidentally touching the control buttons. Measuring beam with double hook. Both contact faces in a single plane.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

1 battery No. 081560 size CR2032.

Optional extras:

Data cable No. 498940.

Technical description

Cross-section measuring beam	12 × 3.5 mm
Number of batteries contained	1
Bridge length	150 mm
Reversible reading	mm / inch
Measuring range	0 - 300 mm
Article no of the battery / rechargeable battery fitted	081560 CR2032
Calibration	A2

Reversible reading	0.0005 in
Power supply	Battery-powered
IP Index of Protection	IP 67
Measurement deviation E MPE	±0.04 mm
Reversible reading	0.01 mm
Standard	ISO 13385
Interface	USB interface
Interface	USB interface
Interface	Digimatic interface
Measured value saving	MAHR reference-lock system
Measurement technology	digital
Material	Stainless steel, INOX
Packaging	Wallet
Type of product	Groove depth gauge

Services

Calibration Vernier hook depth gauge maximum measuring range 300 mm	021220 300
DAkkS calibration Calipers / depth gauges maximum measuring range 300 mm	021010 300

Accessories

Button cell / special battery Battery type CR2032	081560 CR2032
Battery compartment cover	412235