

Single test pin Tolerance class 1, Type: 11



Order data

Order number	483940 11
GTIN	2050002076686
Item class	48A

Description

Version:

Test pins of alloyed tool steel 60 ± 2 HRC. Pin: Hardened, tempered, ground, and lapped. Handle: \emptyset value engraved.

Note:

When ordering, please **additionally state the desired \emptyset** , e.g. No. 483940 size 2 **0.35**.

Technical description

Overall length	95 mm
Test length	60 mm
Nominal size	14 - 15.99 mm
Pitch	0.01 mm
Calibration	L5
Standard	DIN 2269
Tolerance class	1
Hardness	60 ± 2 HRC
Material	alloyed tool steel
Type of product	Test pin

Services

Calibration Test pin maximum \emptyset 20	028240 20
	028260 20

DAkKS calibration Test pin maximum \varnothing 20
