

## Single test pin Tolerance class 2, Type: 10



### Order data

Order number	483941 10
GTIN	2050002077034
Item class	48A

### Description

#### Version:

Test pins of alloyed tool steel  $60 \pm 2$  HRC. Pin: Hardened, tempered, ground, and lapped. Handle:  $\emptyset$  value engraved.

#### Note:

When ordering, please **additionally state the desired  $\emptyset$** , e.g. No. 483940 size 2 **0.35**.

### Technical description

Overall length	95 mm
Test length	60 mm
Pitch	0.01 mm
Nominal size	12 - 13.99 mm
Calibration	L5
Standard	DIN 2269
Tolerance class	2
Hardness	$60 \pm 2$ HRC
Material	alloyed tool steel
Type of product	Test pin

### Services

Calibration Test pin maximum $\emptyset$ 20	028240 20
	028260 20

DAkKS calibration Test pin maximum  $\varnothing$  20

---