

## Single test pin with handle, 3 digits Tolerance class 1, Type: 6



### Order data

Order number	483942 6
GTIN	2050002077140
Item class	48A

### Description

#### Version:

Test pins of alloyed tool steel  $60 \pm 2$  HRC. Pin: Hardened, tempered, ground, and lapped. Handle:  $\emptyset$  value engraved.

#### Note:

When ordering, please additionally state **the desired  $\emptyset$** , e.g. No. 483942 size 3, 0.305.

### Technical description

Test length	33 mm
Nominal size	2.001 - 2.999 mm
Pitch	0.001 mm
Calibration	L5
Overall length	53 mm
Standard	DIN 2269
Tolerance class	1
Hardness	$60 \pm 2$ HRC
Material	alloyed tool steel
Type of product	Test pin

### Services

Calibration Test pin maximum $\emptyset$ 20	028240 20
	028260 20

DAkKS calibration Test pin maximum  $\varnothing$  20

---