

Single test pin with handle, 3 digits Tolerance class 1, Type: 2



Order data

Order number	483942 2
GTIN	2050002077102
Item class	48A

Description

Version:

Test pins of alloyed tool steel 60 ± 2 HRC. Pin: Hardened, tempered, ground, and lapped. Handle: \emptyset value engraved.

Note:

When ordering, please additionally state **the desired \emptyset** , e.g. No. 483942 size 3, 0.305.

Technical description

Overall length	53 mm
Pitch	0.001 mm
Calibration	L5
Nominal size	0.201 - 0.299 mm
Test length	33 mm
Standard	DIN 2269
Tolerance class	1
Hardness	60 ± 2 HRC
Material	alloyed tool steel
Type of product	Test pin

Services

Calibration Test pin maximum \emptyset 20	028240 20
	028260 20

DAkKS calibration Test pin maximum \varnothing 20
