



## ONE-KEY™ cordless drill / driver, Type: M18ODD3-5



### Order data

Order number	070212 M18ODD3-5
GTIN	4058546476731
Item class	03L

### Description

#### Version:

**MILWAUKEE – Cordless drill / driver** Powerful cordless 2-speed drill / driver, reversible. REDLITHIUM™ rechargeable batteries with **single-cell monitoring** and **charge status display**. Sturdy **metal gearbox** for long working life. **FIXTEC metal quick-clamping drill chuck** with spindle lock. LED illumination of the working area. Handle with Softgrip coating for comfortable use. Top model FUEL™ with **brushless POWERSTATE™ motor** for very high efficiency. **Very low wear** and up to 10 times the working life of standard DC motors. The high efficiency and the enhanced battery capacity permit **up to 2× longer operating times** (compared to other Li-ion technologies). **REDLINK PLUS™ electronics** – for unique power management:

- **With system communication between the drive machine and battery.**
- **With overload protection for longer working life of the battery, motor, and gearbox.**

M18 FUEL™ **ONE-KEY™** Cordless drill / driver with high torque.

#### Supplied with:

Supplied with 2× M18 Red-Li-ion rechargeable batteries, M12-18 FC charger, belt clip, HD box (carrying case). Supplied with additional handle for easier support of the torque forces.

#### Note:

See No. 073816, No. 073827 and No. 073840 ff. for suitable replacement batteries and chargers.

### Technical description

maximum vibration to EN	<2,5 m/s <sup>2</sup>
typical application	Heavy Duty
Motor design	Brushless motor
Weight	2.1 kg
Battery voltage	18 V
maximum twist drill size Ø in wood	89 mm
maximum twist drill size Ø in steel	16 mm
Type of rechargeable battery	Lithium-ion
maximum speed 1st speed	0 - 500 min <sup>-1</sup>
maximum torque hard	158 Nm
Number of rechargeable batteries contained	2
maximum speed 2nd speed	2100 min <sup>-1</sup>
Manufacturer's designation	M18 ONEDD3-502X
App link	OneKey
Power supply	Rechargeable battery-powered
suitable battery - supplier / battery type / voltage	Milwaukee type B 18 V
Packaging	Modular case (HD=Heavy Duty)
Battery capacity	5 Ah
Quick-clamping chuck range	1.5 - 13 mm
Type of product	Drill/driver
USP1	18V, ONE-KEY app link
USP2	Brushless motor, with 2 batteries, in a case