

# Yale

Hydraulic hand pump HPS, Number of steps / Tank volume: 2/0,7l



## Order data

Order number	086050 2/0,7
GTIN	4025092159098
Item class	08Y

## Description

### Version:

All components and attachments satisfy **metric standard ranges**, which considerably simplifies assembly, service, and the procurement of spare parts. **100 % compatibility** with all commercially-available 700 bar hydraulic systems.

2-stage hand pump **with rapid movement setting** (except size 1/0.7). The switch from first to second stage is performed automatically. **With pressure limiting valves adjustable in the range 0 – 700 bar. All-metal construction** with fine-adjustment release valve, bleeding and filling screw and a carrying eye on the operating handle.

### Supplied with:

Filled with oil, without manometer.

### Note:

**Closed systems are pre-mounted ex works, filled and air bled.**

For hydraulic hand pump see No. 086050, hydraulic hose No. 086081, pressure gauge No. 086087.

## Technical description

Weight	7 kg
Delivery quantity per no-load stroke (1st stage)	11 ml
usable tank volume	700 ml
Delivery quantity per load stroke (2nd stage)	2 ml

Number of pressure stages	2
Type of product	Hydraulic hand pump

---

## Accessories

Manometer kit GYA-63 Display range 0-1000 bar	086087 0-1000
---	---------------