




Digital universal caliper set IP 67, Measuring range: 200mm



Order data

Order number	415555 200
GTIN	4029713019235
Item class	46P

Description

Version:

"Pocket Talent" digital universal caliper for a wide variety of internal and external measurements (recesses, grooves, threads etc.). Easy-to-read, high-contrast LCD display with 7.5 mm character height. Including a PRESET function (measured value pre-setting).

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

Digital caliper, 50 mm setting gauge, 2 pairs of measuring tips for internal and external measurements. 1 battery No. 081560 size CR2032.

Optional extras:

All spare and special contact points No. 434900 to 434915 with M2.5 thread. Data cable No. 498940.

Technical description

Battery type	Button cell
Error limit	0.03 mm
Jaw length	48 mm
Scale divisions	0.0005 in
Number of batteries contained	1
Power supply	Battery-powered

Article no of the battery / rechargeable battery fitted	081560 CR2032
Scale divisions	0.01 mm
IP Index of Protection	IP 67
Measuring range	0 - 200 mm
Standard	Manufacturer's standard
Reversible reading	mm / inch
Interface	Digimatic interface
Interface	RS232C interface
Interface	USB interface
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Calibration	A1
Type of product	Universal calipers

Services

CalibrationCalipers / depth gauges maximum measuring range 200 mm	021000 200
DAkkS calibrationCalipers / depth gauges maximum measuring range 200 mm	021010 200

Accessories

Button cell / special battery Battery type CR2032	081560 CR2032
---	---------------