

**Multi-purpose oil, Contents: 400ml**

Order data

Order number	083000 400
GTIN	5032227690042
Item class	08E

Description**Version:**

WD-40 multi-function oil is proven world-wide, **almost completely odourless, uses non-polluting propellant**, is Teflon, resin, silicone, and acid-free.

Application:

- **Rust remover with penetrating capillary effect** – quickly releases seized bolts and nuts.
- **Cleaner: loosens stubborn dirt, without sticking or gumming up.**
- **Lubricant for all sliding surfaces, precision mechanics, hinges, Bowden cables, locks and catches.**
- **Corrosion protection: WD-40 penetrates under moisture and into the pores of the material to be protected, thus preserving it. Delicate and expensive tools retain their value.**
- **Contact spray: displaces moisture from electrical components.**

Note:

Approved by: **Rolls Royce, Daimler, Airbus, VW** amongst others.

Not available in all countries. Express delivery not possible.

Technical description

Spray head	Standard
Labelling of hazardous substances	GHS02: Flame
Labelling of hazardous substances	GHS07 caution
Colour	pale brown
Flashpoint	47 °C
Boiling point	176 °C
Oxidisation characteristics	no
Solubility in water	insoluble
Kinematic viscosity	< 1 mm ² /s
Storage temperature	15 - 50 °C
Contents	0.4 l
Version	Spray can
Type of product	Multi-function oil / universal oil