

**Garant****APMT 060204 ER, HB7510, Type: ST1400****Order data**

Order number	215646 ST1400
GTIN	4045197601452
Item class	21A

**Description****Note:**

Standard application values for  $a_e = 0.25 \times D$ .  $a_p = 3$  mm,  $a_p$  max = 4 mm.

Corner radius: 0.4 mm

Feed  $f_z$  per tooth: 0.1 mm

**Technical description**

Type	ST1400
Feed $f_z$ per tooth	0.1 mm
Corner radius	0.4 mm
ISO code indexable insert	APMT 060204 ER
Grade	HB7510
Tool material	Carbide
Type of product	Indexable insert for milling

**User data**

	<b>Suitability</b>	<b>V<sub>c</sub></b>	<b>ISO code</b>
Steel < 1100 N/mm <sup>2</sup>	suitable	220 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable	200 m/min	P
wet maximum	suitable only under restricted conditions		
dry	suitable		