

Garant
HiPer-Drill cutter insert h7, HB7630, Ø D: 18,25 mm

Order data

Order number	231650 18,25
GTIN	4045197640604
Item class	21M

Description
Version:

Vee ground cutter inserts for precise positioning and stable seating.
Concentricity when assembled $\leq 20 \mu\text{m}$. For holes up to IT9 accuracy.

Note:

Further sizes available on request. Cutting data apply to 5×D drilling bodies.

Use exclusively cutter heads of the same type when drilling pilot holes.

for base body Ø D: 18 mm

Feed f in stainless steel $> 900 \text{ N/mm}^2$: 0.2 mm/rev.

Technical description

Ø D	18.25 mm
for base body Ø D	18 mm
Feed f in stainless steel $> 900 \text{ N/mm}^2$	0.2 mm/rev.
Number of changes/inserts	1
Grade	HB7630

Tool material	Carbide
Point angle	135 degrees
Number of cutting edges Z	2
Type of product	Cutter insert for boring

Accessories

Torx Plus® screw Drive 8IP1	231999 8IP1
-----------------------------	-------------