

**Garant**
**Chamfer mill, with bore, Angle  $\gamma$ : 15°**

**Order data**

Order number	215700 15
GTIN	4045197410504
Item class	210

**Description**
**Note:**

- **Recommended milling inserts for chamfering: No. 215720; 215724; 215728; 215744; 215758.**
- **If other milling inserts are used, the tool life may be less and surface quality may suffer.**
- **Use GARANT torque screwdriver TQ No. 211750 size 5.0 with bit No. 674252 size 15IP.**

**Technical description**

suitable indexable insert	AP.. 1604..
Pack of insert screws	219811 (15IP; 5.0 Nm)
achievable chamfer length l	30 mm
Overall length $L_{tot}$	50 mm
Number of effective inserts $Z_{eff}$	3
achievable chamfer width b	29.5 mm
largest $\varnothing D_1$	94 mm

achievable chamfer height h	8 mm
Mounting bore Ø	27 mm
smallest Ø D	35.4 mm
Angle $\gamma$	15 degrees
Feed rate per tooth at $h_{\max}$	0.4 mm
Number of indexable inserts	6
Shank type	with bore
Through-coolant	yes
Tool exchange	PowerCard
Type of product	Indexable end mill

## Accessories

PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 15IP	674252 15IP
Set of insert screws 10-piece	219811
Torque screwdriver, fixed setting set torque 5,0 N·m	211750 5,0