



## Multi-purpose oil, Contents: 500 ml



### Order data

Order number	083000 500
GTIN	5032227690349
Item class	08E

### Description

#### Version:

WD-40 multi-function oil is proven world-wide, **almost completely odourless, uses non-polluting propellant**, is Teflon, resin, silicone, and acid-free.

#### Application:

- **Rust remover with penetrating capillary effect – quickly releases seized bolts and nuts.**
- **Cleaner: loosens stubborn dirt, without sticking or gumming up.**
- **Lubricant for all sliding surfaces, precision mechanics, hinges, Bowden cables, locks and catches.**
- **Corrosion protection: WD-40 penetrates under moisture and into the pores of the material to be protected, thus preserving it. Delicate and expensive tools retain their value.**
- **Contact spray: displaces moisture from electrical components.**

With variable spray tube angle, for spreading or pin-point application. Can be used only in one of two positions (0°, 90°).

#### Note:

Approved by: **Rolls Royce, Daimler, Airbus, VW** amongst others.

Not available in all countries. Express delivery not possible.

Version: Spray can

Labelling of hazardous substances: GHS02 flammable

Labelling of hazardous substances: GHS07 Caution

hazardous goods class: 2.1  
Spray head: Smart Straw

## Technical description

Spray head	Smart Straw
Labelling of hazardous substances	GHS02 flammable
Labelling of hazardous substances	GHS07 Caution
Colour	pale brown
Oxidisation characteristics	no
hazardous goods class	2.1
Boiling point	176 °C
UN number	UN1950
Solubility in water	insoluble
Flashpoint	47 °C
Kinematic viscosity	< 1 mm <sup>2</sup> /s
Storage temperature	15 - 50 °C
Contents	0.5 l
Version	Spray can
Type of product	Multi-function oil / universal oil