

# Yale

## Hydraulic hand pump HPS, Number of steps / Tank volume: 2/2l



### Order data

Order number	086050 2/2
GTIN	4025092159104
Item class	08Y

### Description

#### Version:

All components and attachments satisfy **metric standard ranges**, which considerably simplifies assembly, service, and the procurement of spare parts. **100 % compatibility** with all commercially-available 700 bar hydraulic systems.

2-stage hand pump **with rapid movement setting** (except size 1/0.7). The switch from first to second stage is performed automatically. **With pressure limiting valves adjustable in the range 0 – 700 bar. All-metal construction** with fine-adjustment release valve, bleeding and filling screw and a carrying eye on the operating handle.

#### Supplied with:

Filled with oil, without manometer.

#### Note:

**Closed systems are pre-mounted ex works, filled and air bled.**

For hydraulic hand pump see No. 086050, hydraulic hose No. 086081, pressure gauge No. 086087.

### Technical description

usable tank volume	2000 ml
Delivery quantity per load stroke (2nd stage)	2 ml
Number of pressure stages	2
Delivery quantity per no-load stroke (1st stage)	11 ml

Weight	10 kg
Type of product	Hydraulic hand pump

---

## Accessories

Manometer kit GYA-63 Display range 0-1000 bar	086087 0-1000
---	---------------