

Garant

Solid carbide arbor configurable, for cutter head Ø D: 20mm



Order data

Order number	212000 20
GTIN	4045197659248
Item class	29W

Description

Version:

Precision-ground arbor for GARANT TopCut screw-in heads.

System radial run-out $\leq 10 \mu\text{m}$ due to the combination of taper and flat face.

Shank ground to h6 over its entire length – for individual cutting out and cutting to length.

Note:

Maximum milled depth = $L_1 + l$; l = see dimensions of the screw-in heads: No. 210050 – 210410.

Assembly wrench = No. 219987.

Plug-in adapter for torque wrench = No. 219986.

For long tool overhang, reduce technology data.

The shank can also be cut back to $\varnothing d_{1 \text{ min}}$.

Technical description

for cutter head Ø D	20 mm
Shank Ø D _s h6	20 mm
minimum available external Ø d ₁	19.8 mm
Reach L ₁	40 mm
recommended tightening torque	25 Nm
Overall length L	195 mm
Series	TopCut
Through-coolant	yes
Type of product	Threaded copy mill arbor

