

AEG**Cordless drill / driver, Type: BS12C2**

Order data

Order number	070221 BS12C2
GTIN	4002395294336
Item class	07A

Description**Version:****AEG – Cordless drill / driver**

- Sturdy and handy cordless 2-speed drill / screwdriver, reversible.
- FIXTEC quick-change chuck with spindle lock.
- Handle with Softgrip coating for comfortable use.
- LED illumination of the working area.
- Extremely compact - only 176 mm overall length.
- 17-step torque limit adjustment, plus drill steps.
- 10 mm quick-change chuck.
- Metal gearbox casing, electronic overload protection.

Version of the advertising text:

- Sturdy and handy cordless 2-speed drill / driver, reversible.
- FIXTEC quick-change chuck with spindle lock.
- Handle with Softgrip coating for comfortable use.
- Extremely compact - only 176 mm overall length.
- 17-step torque limit adjustment, plus drill steps.

Advantage:

Extremely compact, only 176 mm overall length.

Supplied with:

Supplied with 2 pcs. 12 V / 2.0 Ah battery, charger, transport case.

Attention:

German version. Order free UK adapter plug No. 08 1172_GB.

Note:

See No. 073820 and No. 073846 – No. 073848 for suitable replacement batteries and chargers. Suitable chargers and starter sets can be found under No. 073841 and No 073844.

Technical description

Motor design	2-pole motor
maximum twist drill size Ø in wood	20 mm
Weight	1.1 kg
maximum speed 2nd speed	1500 min ⁻¹
Quick-clamping chuck range	1.5 - 10 mm
Manufacturer's designation	BS 12 C2
maximum torque hard	34 Nm
Battery capacity	2 Ah
maximum twist drill size Ø in steel	10 mm
Battery voltage	12 V
typical application	Medium
maximum vibration to EN	< 2.5 m/s ²
maximum speed 1st speed	0 - 350 min ⁻¹
suitable battery - supplier / battery type / voltage	AEG type B 12 V
Packaging	Carrying case
Number of rechargeable batteries contained	2
Type of rechargeable battery	Lithium-ion
Power supply	Rechargeable battery-powered
Suitable for material	Steel
Suitable for material	wood
Type of product	Drill/driver
USP1	12V, 2-pole motor

USP2

FIXTEC quick-change
chuck, with 2 batteries

Accessories

Li-ion system L1220 Battery type AB12

073825 AB12

Battery charger Type BL1418

073841 BL1418