

Garant
Shoulder mill 90°, Weldon shank, Ø D / Zeff: 32/2mm

Order data

Order number	215860 32/2
GTIN	4045197133304
Item class	210

Description
Version:

Very high metal removal rate, as 2 or 3 cutting edges are in action during each rotation.

Application:

For peripheral milling and side milling.

Note:

Not for ramping or circular plunging!

Use GARANT torque screwdriver TQ No. **211750 size 1.2** with bit No. **674252 size 8IP**.

Technical description

Overhang L_1	54 mm
Cutting edge $\varnothing D_c$	32 mm
Pack of insert screws	219814 (8IP; 1.2 Nm)
Overall length L_{tot}	114 mm
Number of effective inserts Z_{eff}	2
suitable indexable insert	AP.. 1003
maximum cutting depth $a_{p,max}$	38 mm
Shank $\varnothing D_s$ h6	32 mm
Number of indexable inserts	8
Shank type	Weldon shank

Setting angle κ	90 degrees
Milling application	End milling
Through-coolant	yes
Machining strategy	MTC
Tool exchange	PowerCard
Type of product	End / face mill

Accessories

PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 8IP	674252 8IP
Torque screwdriver, fixed setting set torque 1,2 N·m	211750 1,2
Set of insert screws 10-piece	219814