



Cordless special drill / driver, Type: C12RAD



Order data

Order number	070225 C12RAD
GTIN	4002395001248
Item class	03L

Description

Version:

MILWAUKEE – cordless right angle drill and ratchet

- **REDLINK™ electronics with stepless speed control, reversible running and overload protection.**
- **LED illumination of the working area.**
- **Red Li-ion batteries with single-cell monitoring and charge display.**

Lightweight and handy compact **right angle** drill / driver for places where access is difficult, very compact – **only 95 mm width across head**. 10-stage electronic torque adjustment plus drill step, **FIXTEC** quick-release chuck. A red LED indicates the torque that has been reached.

Advantage:

Very compact, only 95 mm width across head.

Supplied with:

Includes a battery, charger and transport case.

Note:

See No. 073814 and No. 073839 for suitable batteries and chargers.

Technical description

Battery capacity	2 Ah
Format	Right angle drill / driver
maximum twist drill size Ø in wood	25 mm
Manufacturer's designation	C12RAD-202B
maximum vibration to EN	< 2.5 m/s ²

maximum speed 1st speed	0 - 800 min ⁻¹
Weight	1.1 kg
Toolholder	Ø 1.0 – 10 mm
Battery voltage	12 V
maximum torque hard	12 Nm
typical application	Medium
maximum twist drill size Ø in steel	10 mm
suitable battery - supplier / battery type / voltage	Milwaukee type B 12 V
Number of rechargeable batteries contained	2
Power supply	Rechargeable battery-powered
Type of rechargeable battery	Lithium-ion
Suitable for material	wood
Suitable for material	Steel
Type of product	Screwdriver

Accessories

Battery charger Type M1218C	073840 M1218C
Battery charger Type M1218FC	073840 M1218FC
Li-ion system M4B2/M12B2 Battery type MB12	073814 MB12