



Indexable milling cutter 90°, with threaded shank, Ø D / number of teeth Z: 25/3_ mm

Order data

Order number	215870 25/3_
GTIN	4045197195395
Item class	210

Description

Description:

General application in all materials and for slot milling. Arbors for milling cutters with thread see catalogue section 3.

Application:

General application in all materials and for slot milling.

Note:

Arbors for milling cutters with thread see catalogue section 3.

Use GARANT torque screwdriver TQ No. **211750 size 1.2** with bit No. **674252 size 8IP**.

Setting angle κ : 90 degrees

Milling application: Circular milling

Milling application: Ramping

Milling application: End milling

Through-coolant: true

Machining strategy: MTC

Technical description

Setting angle κ	90 degrees
Shank type	with threaded shank
Milling application	Circular milling
Milling application	Ramping
Milling application	End milling
Tool exchange	PowerCard
Machining strategy	MTC
Through-coolant	yes

Spacing of the cutters

Type

Norm

Type of product
