

HEDI

Cable reel, Type: 10N



Order data

Order number	081194 10N
GTIN	4003644016969
Item class	08B

Description

Version:

Cable reel with **guided automatic draw-in and roll-up, with multiple stop points per revolution**. High-impact enclosed **plastic housing**. Thermal **overload cut-out**, sturdy H07RN-F neoprene cable with connection point.

Easy to mount on the wall or ceiling with **150° pivoting range**.

Function:

IP24: Protected against splashed water from all directions and protected against penetration by foreign bodies with $\varnothing < 12$ mm, however touching should be avoided.

Application:

Improved ergonomics by relieving cable tension, and for ensuring tidiness and avoiding the risk of accidents and injuries due to cables lying on the ground.

Note:

For spring return hose reels see No. 080066 to 080079.

Technical description

Body material	Plastic
Height	275 mm
Type	10N
Cable structure	3G1.5

Material cable	Neoprene rubber
Width	185 mm
Rated power unrolled	2000 (16 A) W
Length	325 mm
Cable class	H07RN-F
Cable length	10 m
Nominal voltage	250 V
IP Index of Protection	IP 24
Power supply	Mains operated
Plug type, input	F
Type of product	Cable reel