



Angle grinder Cordless, Type: M18CAGXPD



Order data

Order number	077140 M18CAGXPD
GTIN	4002395263479
Item class	03L

Description

Version:

18 V / 5.0 Ah FUEL™ Milwaukee cordless angle grinder:

- **long-life brushless motor, spindle locking, quick adjustment of the safety guard.**
- **Integral FIXTEC quick-release system for changing discs without using tools.**

Supplied with:

Supplied with charger, safety guard, 2 dust-protection grilles, clamping set, anti-vibration handle, HD box.

Note:

See from No. 073809 and No. 073840 for suitable replacement batteries and accessories.

Packaging: Modular case (HD=Heavy Duty)

suitable battery - supplier / battery type / voltage: Milwaukee type B 18 V

suitable battery - supplier / battery type / voltage: Milwaukee type HB 18 V

Manufacturer's designation: M18CAG125XPD-502X

Number of rechargeable batteries contained: 2

Type of rechargeable battery: Lithium-ion

Battery capacity: 5 Ah

Battery voltage: 18 V

maximum speed: 8500 rpm

Technical description

Battery capacity	5 Ah
Quick-release clamping nut	yes

Battery voltage	18 V
Weight	2.7 kg
maximum speed	8500 rpm
Kick-back stop	no
Motor design	brushless EC motor
maximum vibration to EN	3.4 m/s ²
Dead man's circuit	yes
maximum disc Ø	125 mm
Soft start	yes
maximum cutting depth	33 mm
Manufacturer's designation	M18CAG125XPD-502X
Restart block	yes
suitable battery - supplier / battery type / voltage	Milwaukee type B 18 V
suitable battery - supplier / battery type / voltage	Milwaukee type HB 18 V
Overload protection	yes
Type of rechargeable battery	Lithium-ion
Number of rechargeable batteries contained	2
Packaging	Modular case (HD=Heavy Duty)
Power supply	Rechargeable battery-powered
Type of product	Angle grinder

Accessories

Battery charger Type M1218C	073840 M1218C
Battery charger Type M1218FC	073840 M1218FC
Li-ion system M18B5 Rechargeable battery type, battery voltage MB18 V	073816 MB18