



Magnetic vice set VersaMAG, Type: VERSA-01



Order data

Order number	P07030 VERSA-01
GTIN	4014586896564
Item class	03F

Description

Version:

Compact and powerful permanent magnet with vice for clamping various components on magnetic surfaces without the need for any tools.

- **Mobile, flexible and swift use. Adapts to every workstation thanks to the compact design and extra-narrow permanent magnet.**
- **Optimises every workstation: clean and reliable working with versatile application options.**
- **Modular system: the unique modular system ensures a secure hold in a very wide range of work situations and the right accessories can be added at any time.**
- **The vice has a clamping range of 108 mm and a jaw width of 100 mm.**
- **Interchangeable clamping jaws of various heights for clamping larger materials such as sheet metal and pipes.**
- **Up to 7800 N of holding force for reliable clamping on all magnetic surfaces thanks to an innovative 2-rotor system – even when working with thin sheet metal (from a thickness of 4 mm).**
- **Clamping in tight spots or on vertical planes? Not a problem thanks to the compact design and extra-narrow permanent magnet.**
- **30% magnetic bias for precise alignment of the permanent magnet.**
- **Secure clamping of components for further machining with various power tools, e.g. angle grinders, drill/drivers, saws, MULTIMASTER.**

Supplied with:

1 pc. permanent magnet, 1 pc. mounting plate, 1 pc. vice, 1 pc. 3 mm hexagon L-wrench, 1 pc. lashing strap.

Technical description

Length A	212 mm
Weight	7.25 kg
Width B	70 mm
Jaw width	100 mm
Jaw height	40 mm
Magnet retaining force	7800 N
Type of product	Magnetic clamping plate