



## KOMET KUB Centron® drill head, Ø DC: 44mm



### Order data

Order number	236650 44
GTIN	4047109025752
Item class	24L

### Description

#### Version:

- Process reliable up to 8 (9)×D.
- Centring by centring point and slide bars.
- Stiff joint between base body and drill head.
- Ø of the slide bars is matched to indexable inserts with 0.4 mm edge radii. For through holes the Ø of the slide bars can be adjusted by means of shims.

#### Application:

- For rotating and stationary as well as vertical and horizontal use in all materials.
- With centring tips No. 236655 – 236657.
- With indexable inserts No. 236740 – 237080.

#### Suitable for:

Base body No. 236652 – 236654.

#### Supplied with:

Drill head including slide bars (spare slide bars No. 236658).

From Ø 65 mm with indexable insert cartridges (cartridge for the outer indexable insert adjustable + 1 mm on the Ø).

### Technical description

Pack of insert screws	239655 8IP2 (1.3 Nm)
-----------------------	----------------------

ISO code indexable insert	WOEX 05T304
Base body size	40
Number of cutting edges Z	1
Screw for base body	239655 20IP1
Centring tip size	40
Series	KUB Centron®
Nominal Ø D	44
Use for drilling	Centre drilling
Use for drilling	limited cross-drilling
Use for drilling	limited drilling with oblique exit
Use for drilling	limited cross-drilling
Through-coolant	yes
Type of product	Indexable drill

## Accessories

Torx Plus® insert screw set10 pieces Drive 8IP2	239655 8IP2
KOMET® base body Ø DC 40 mm	236654 40
Torque screwdriver, fixed setting set torque 1,3 N·m	211750 1,3
PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 8IP	674252 8IP
KOMET® base body Ø DC 40 mm	236652 40
KOMET® base body Ø DC 40 mm	236653 40
KOMET KUB Centron® centring point, carbide Type 40	236657 40
Torx Plus® insert screw set10 pieces Drive 20IP1	239655 20IP1
Torx Plus® insert screw set10 pieces Drive 20IP	239655 20IP
KOMET KUB Centron® centring point, HSS Type 40	236655 40
KOMET KUB Centron® centring point, HSS Type 40	236656 40