



MultiMaster 5 combination ladder, Number of steps: 5



Order data

Order number	966101 5
GTIN	4003866403318
Item class	96Z

Description

Version:

One ladder, 5 modes: stepladder, stair stepladder, off-set mode single ladder, single ladder and extended single ladder.

Quick and easy one-handed switching between modes, and finely adjustable rear section with 35 mm increments.

Anodised aluminium stiles, 80 mm deep treads with Safer Step Technology. Riveted step-stile connection. Ergonomic transport thanks to 2 wheels on the ascending part. Specially shaped top with handle. Increased flexibility and versatility as top can be used on inner and outer corners as well as on masts. Top with magnetic compartment for small parts as well as 2 clip holders and central recess for cordless screwdrivers or similar tools.

Standard:

DIN EN 131-4.

Technical description

Rung/step depth	80 mm
Width closed	0.64 m

Number of steps	5
Weight	11.4 kg
Standard	DIN EN 131-4.
Length closed	1.83 m
Ladder length as a stepladder	1.83 m
Stepladder working height approx.	3.15 m
Ladder length extended	2.88 m
Depth closed	0.23 m
Storage tray available	yes
wheeled	yes
Series	MultiMaster
Lean-to ladder working height approx.	3.7 m
Type of step	step
Material	Aluminium
Ladders and platforms load capacity	150 kg
Type of product	Multi-purpose ladder