

HEDI

Cable reel, Type: 15N



Order data

Order number	081194 15N
GTIN	4003644016990
Item class	08B

Description

Version:

Cable reel with **guided automatic draw-in and roll-up, with multiple stop points per revolution**. High-impact enclosed **plastic housing**. Thermal **overload cut-out**, sturdy H07RN-F neoprene cable with connection point.

Easy to mount on the wall or ceiling with **150° pivoting range**.

Application:

Improved ergonomics by relieving cable tension, and for ensuring tidiness and avoiding the risk of accidents and injuries due to cables lying on the ground.

Note:

For spring return hose reels see No. 080066 to 080079.

Technical description

Cable class	H07RN-F
Type	15N
Material cable	Neoprene
Cable length	15 m
Width	185 mm
Length	325 mm

Cable structure	3G1.5
Rated power unrolled	2000 (16 A) W
Height	275 mm
Body material	Plastic
Nominal voltage	250 V
Power supply	Mains operated
Plug type, input	F
Type of product	Cable reel