



Swing door cabinet set with plain sheet metal swing doors, Number of cabinets: 2



Order data

Order number	949502 2
GTIN	4067263107781
Item class	90N

Description

Version:

Body and doors made of sheet metal, storage shelf mountings at 40 mm intervals. Doors reinforced on the inside and can be locked by push handle with a **cylinder lock**. For more information on locking see No. 950050 – 950060.

With plain sheet metal swing doors.

Supplied with:

2x No. 949501 size 2000.

Colour:

Body light grey RAL 7035, doors signal blue RAL 7016 **powder-coated**.

Note:

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Width	1000 mm
Weight	69 kg

Data sheet

Depth	400 mm
Electronic locking system can be retrofitted	yes
Handle positioning	centre
Height	2000 mm
Usable height	1840 mm
Cabinet fronts	Plain sheet metal swing door
Number of shelves	4
Material thickness	0.9 mm
Shelf load capacity / maximum distributed shelf load (on metal)	60 kg
Cabinet housing internal load capacity	500 kg
Door opening angle	225 degrees
Height adjustment interval	40 mm
Cylinder lock	modular barrel
Colour selection	RAL 7035, RAL 7016, RAL 5005
Type of product	Filing cabinet

Accessories

Additional storage shelf Type 1000	949514 1000
------------------------------------	-------------