



## Swing door cabinet set with storage shelves, Number of cabinets: 2



### Order data

Order number	949532 2
GTIN	4067263107798
Item class	90N

### Description

**Version:**

Body and doors made of sheet metal, storage shelf mountings at 40 mm intervals. Doors reinforced on the inside and can be locked by push handle with a **cylinder lock**. Complete with **4 shelves** made of galvanised sheet metal.

**Supplied with:**

2× No. 949531 size 1950/A.

**Colour:**

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

**Note:**

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

### Technical description

Handle positioning	centre
Number of shelves	4
Depth	430 mm

## Data sheet

Height	1950 mm
Model	A
Usable height	1820 mm
Weight	74 kg
Cabinet fronts	Plain sheet metal swing door
Width	950 mm
Material thickness	0.9 mm
Shelf load capacity / maximum distributed shelf load (on metal)	80 kg
Cabinet housing internal load capacity	500 kg
Door opening angle	250 degrees
Height adjustment interval	40 mm
Cylinder lock	modular barrel
Colour selection	RAL 7035, RAL 7016, RAL 5005
Type of product	Filing cabinet

## Accessories

Additional storage shelf Type 950	949534 950
-----------------------------------	------------