


KOMET KUB Centron® drill head, Ø DC: 64mm

Order data

Order number	236650 64
GTIN	4047109081772
Item class	24L

Description
Version:

- **Process reliable up to 8 (9)×D.**
- **Centring by centring point and slide bars.**
- **Stiff joint between base body and drill head.**
- **Ø of the slide bars is matched to indexable inserts with 0.4 mm edge radii. For through holes the Ø of the slide bars can be adjusted by means of shims.**

Application:

- **For rotating and stationary as well as vertical and horizontal use in all materials.**
- **With centring tips No. 236655 – 236657.**
- **With indexable inserts No. 236740 – 237080.**

Suitable for:

Base body No. 236652 – 236654.

Supplied with:

Drill head including slide bars (spare slide bars No. 236658).

From Ø 65 mm with indexable insert cartridges (cartridge for the outer indexable insert adjustable + 1 mm on the Ø).

Technical description

Number of cutting edges Z	1
---------------------------	---

Base body size	55
Pack of insert screws	239655 15IP (6.3 Nm)
Screw for base body	239655 20IP2
ISO code indexable insert	WOEX 080404
Centring tip size	46
Series	KUB Centron®
Nominal Ø D	64
Use for drilling	Centre drilling
Use for drilling	limited cross-drilling
Use for drilling	limited drilling with oblique exit
Use for drilling	limited cross-drilling
Through-coolant	yes
Type of product	Indexable drill

Accessories

KOMET® base body Ø DC 55 mm	236654 55
8 mm blade with magnet with 1/4 inch bit holder overall length 50 mm	659874 50
KOMET® base body Ø DC 55 mm	236652 55
Torx Plus® insert screw set 10 pieces Drive 15IP	239655 15IP
KOMET KUB Centron® centring point, HSS Type 46	236656 46
KOMET KUB Centron® centring point, carbide Type 46	236657 46
Torx Plus® insert screw set 10 pieces Drive 20IP2	239655 20IP2
PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 15IP	674252 15IP
KOMET® base body Ø DC 55 mm	236653 55
KOMET KUB Centron® centring point, HSS Type 46	236655 46