


VNMG 160408, Grade: CA6525

Order data

| | |
|--------------|---------------|
| Order number | 251754 CA6525 |
| GTIN | 4960664513215 |
| Item class | 25E |

Description

VNMG 160408 CA6525 Grade: CA6525
 Chip breaker: MQ
 Cutting depth a_p : 0.5 - 1.5 mm
 Feed f : 0.05 - 0.25 mm/rev.
 Cutting speed v_c main application: 60 - 220 m/min

Technical description

| | |
|--------------------------------------|----------------------|
| Cutting depth a_p | 0.5 - 1.5 mm |
| Main application | M |
| Corner radius | 0.8 mm |
| Cutting speed v_c main application | 60 - 220 m/min |
| Cutting conditions | slightly interrupted |
| Feed f | 0.05 - 0.25 mm/rev. |
| Chip breaker | MQ |

| | |
|-------------------------------|------------------------------|
| Grade | CA6525 |
| Finishing/roughing assignment | Finishing |
| Tool material | Carbide |
| ISO code indexable insert | VNMG 160408 |
| Number of changes/inserts | 4 |
| Type of product | Indexable insert for turning |