

**Garant****CC.T 120408, Grade: HB7020**

## Order data

Order number	260160 HB7020
GTIN	4045197698889
Item class	21G

## Description

CC.T 120408 HB7020 Grade: HB7020  
Chip breaker: SM  
Tolerance: M  
Cutting depth  $a_p$ : 0.2 - 4 mm  
Feed  $f$ : 0.1 - 0.3 mm/rev.  
Cutting speed  $v_c$  main application: 120 - 350 m/min

## Technical description

Cutting speed $v_c$ main application	120 - 350 m/min
Cutting conditions	slightly interrupted
Corner radius	0.8 mm
Chip breaker	SM
Cutting depth $a_p$	0.2 - 4 mm
Main application	P

Feed f	0.1 - 0.3 mm/rev.
Grade	HB7020
Finishing/roughing assignment	Semi-roughing
Tool material	Carbide
ISO code indexable insert	CCMT 120408
Number of changes/inserts	2
Tolerance	M
Type of product	Indexable insert for turning