

Garant**Micro-boring head Digital Ø 0.3 - 19.1 mm****Order data**

Order number	237498
GTIN	4045197816443
Item class	29W

Description**Version:**

Adjustment accuracy 0.01 mm per graduation / with vernier 0.002 mm on the Ø.

Digital boring heads with **additional precise reading facility** on **0.001 mm in Ø** via **digital display unit No. 237601** (order separately).

Ø adjustment with minimum backlash thanks to direct measuring system.

Application:

With cutting insert No. 237621, adapter No. 237624 and insert No. 237625.

Technical description

Reach L ₁	32 mm
Shank Ø D ₂	16 mm
Ø D ₃	7 mm
External Ø D ₁	32 mm
Through-coolant	yes
Type of product	Boring tool

