

Garant
**Digital precision boring set with fine boring head \varnothing 9.75 – 30.1 mm,
Connection: HW63**

Order data

Order number	237566 HW63
GTIN	4045197816672
Item class	29W

Description
Version:

With **digital fine boring head** No. 237568, **digital display unit** No. 237601, boring bars and accessories in a case.

Adjustment accuracy 0.01 mm per graduation / with vernier 0.002 mm on the \varnothing .

With additional precise reading facility to 0.001 mm in \varnothing .

\varnothing adjustment with minimum backlash thanks to direct measuring system.

For \varnothing 9.75 – 30.1 mm

Application:

For boring bars with shank \varnothing 16 mm and precision boring bridges. With ISO indexable inserts **type CC..0602...**

Supplied with:

1 fine boring head: No. 237568 HW63

1 each boring bar (max. boring length): No. 237630 \varnothing 9.75 – 15.1 mm (30 mm), No. 237632 \varnothing 14.75 - 20.1 mm (51 mm);

No. 237634 \varnothing 19.75 – 25.1 mm (72 mm), No. 237636 \varnothing 24.75 - 30.1 mm (82 mm).

1 insert toolholder for the bridge: No. 237564 06

1 insert: No. 260052 size CU7010 (CCMT 060204)

1 digital display unit: No. 237601

Spare part:

Insert screw No. 219830.

Recommendation:

Best with indexable inserts No. 237695 and No. 237696.

Through-coolant: yes

Technical description

Connection	HW63
Power supply	Battery-powered
Article no of the battery / rechargeable battery fitted	081557 LR3
Number of batteries contained	1
Battery type	LR3
Through-coolant	yes
Type of product	Boring tool

Accessories

Insert toolholder for bridges	237565
Boring bar	237632
Boring bar	237634
Boring bar	237636
CC.T 060204 Grade CU7010	260052 CU7010
Fine boring head Ø 9.75 – 88.1 mm Connection HW63	237568 HW63
Boring bar	237630
Set without arbor Ø 9.75 – 164 mm	237598
Display unit digital	237601