

HEDI

Cable reel for F, B, PL, CZ, Type: 10N



Order data

Order number	081195 10N
GTIN	4003644016976
Item class	08B

Description

Version:

Cable reel with **guided automatic draw-in and roll-up, with multiple stop points per revolution**. High-impact enclosed **plastic housing**. Thermal **overload cut-out**, sturdy H07RN-F neoprene cable with connection point.

Easy to mount on the wall or ceiling with **150° pivoting range**.

Function:

IP24: Protected against splashed water from all directions and protected against penetration by foreign bodies with $\varnothing < 12$ mm, however touching should be avoided.

Application:

Improved ergonomics by relieving cable tension, and for ensuring tidiness and avoiding the risk of accidents and injuries due to cables lying on the ground.

Note:

For spring return hose reels see No. 080066 to 080079.

Technical description

Length	325 mm
Cable class	H07RN-F
Rated power unrolled	2000 (16 A) W
Body material	Plastic

Height	275 mm
Material cable	Neoprene rubber
Type	10N
Width	185 mm
Cable structure	3G1.5
Cable length	10 m
Nominal voltage	250 V
IP Index of Protection	IP 24
Power supply	Mains operated
Plug type, input	E
Type of product	Cable reel