


KNUX 160405R Set 10 pieces, Grade: HBX020

Order data

Order number	251050 HBX020
GTIN	4045197663757
Item class	22D

Description

KNUX 160405R Set 10 pieces HBX020 Grade: HBX020

Chip breaker: PM

Chip diverter: 2.2 mm

Cutting depth a_p : 1 - 5 mm

Feed f : 0.2 - 0.7 mm/rev.

Cutting speed v_c main application: 80 - 300 m/min

Technical description

Cutting conditions	slightly interrupted
Main application	P
Feed f	0.2 - 0.7 mm/rev.
Corner radius	0.5 mm
Chip breaker	PM
Chip diverter	2.2 mm
Cutting depth a_p	1 - 5 mm
Grade	HBX020
Cutting speed v_c main application	80 - 300 m/min
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning

Tool material	Carbide
Number of changes/inserts	2
ISO code indexable insert	KNUX 160405R
Type of product	Indexable insert for turning