


KOMET® base body, 4×D, Ø DC: 46mm

Order data

Order number	236653 46
GTIN	4047109095915
Item class	24K

Description
Version:

- Process reliable up to 4×D.
- Stiff joint between base body and drill head.
- Shank type ABS.

Application:

For rotating and stationary as well as vertical and horizontal use in all materials.

Note:

Further sizes and spare parts on request.

Technical description

suitable for drilling head	46 - 54 mm
ABS® shank Ø D _s	80 mm
Base body Ø d ₁	44.5 mm
Overall length L _{tot}	280 mm
Reach L ₁	215 mm
Nominal Ø D	46
Drill depth for indexable insert drill up to	4×D
Shank	ABS
Through-coolant	yes
Type of product	Indexable drill

