


KOMET KUB Centron® Powerline drill head, Ø DC: 34mm

Order data

Order number	236651 34
GTIN	4047109227071
Item class	24L

Description
Version:

The drill point guides the tool precisely on the axis of the hole, thus ensuring both straightness and very high process reliability, with stability in hole depths up to 9×D.

Spot drilling on flat level surfaces without a pilot hole.

Drill head without slide bars and slide bar adjustment.

Application:

For rotating and stationary as well as vertical and horizontal use in all materials.

With centring tip No. 236659.

With indexable inserts No. 236520 – 236576.

Note:

Further sizes available on request.

Technical description

Centring tip size	50
Number of cutting edges Z	2
ISO code indexable insert	SOEX 110508
Pack of insert screws	239652 15IP2 (2.8 Nm)
Screw for base body	239653 15IP
Base body size	33

Series	KUB Centron®
Nominal Ø D	34
Use for drilling	limited cross-drilling
Use for drilling	limited drilling with oblique exit
Use for drilling	limited cross-drilling
Use for drilling	Drilling blind holes
Through-coolant	yes
Type of product	Indexable drill

Accessories

PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 15IP	674252 15IP
Torx Plus® insert screw set10 pieces Drive 15IP	239653 15IP
Torx Plus® insert screw set10 pieces Drive 15IP	239652 15IP
Torque screwdriver, fixed setting set torque 2,8 N·m	211750 2,8