


KOMET® base body, 6×D, Ø DC: 40mm

Order data

Order number	236652 40
GTIN	4047109076297
Item class	24K

Description
Version:

- **Process reliable up to 6×D.**
- **Stiff joint between base body and drill head.**
- **Shank type ABS.**

Application:

For rotating and stationary as well as vertical and horizontal use in all materials.

Note:

Further sizes and spare parts on request.

Technical description

suitable for drilling head	40 - 45 mm
Base body Ø d ₁	38.5 mm
Overall length L _{tot}	310 mm
ABS® shank Ø D _s	63 mm
Reach L ₁	260 mm
Nominal Ø D	40
Drill depth for indexable insert drill up to	6×D
Shank	ABS
Through-coolant	yes
Type of product	Indexable drill

