

**KOMET® base body, 8×D, Ø DC: 72mm****Order data**

Order number	236654 72
GTIN	4047109096011
Item class	24K

Description**Version:**

- **Process reliable up to 8 (9)×D.**
- **Stiff joint between base body and drill head.**
- **Shank type ABS.**

Application:

For rotating and stationary as well as vertical and horizontal use in all materials.

Note:

Further sizes and spare parts on request.

Technical description

Base body Ø d ₁	70.5 mm
suitable for drilling head	72 - 81 mm
Overall length L _{tot}	690 mm
ABS® shank Ø D _s	100 mm
Reach L ₁	610 mm
Nominal Ø D	72
Drill depth for indexable insert drill up to	8×D
Shank	ABS
Through-coolant	yes
Type of product	Indexable drill

