

## Extension cable for F, B, PL, CZ, 250 V, Type: 25N



### Order data

Order number	081183 25N
GTIN	4007123251513
Item class	08B

### Description

#### Version:

**Certified for exterior use and for use in humid environments (IP44).**

With sockets for **countries F, B, PL, CZ**. Resistant to oil, petrol, UV radiation.

**Neoprene rubber cable** with splash-proof rubber plug and socket.

#### Function:

IP20: No protection against penetration by foreign bodies with  $\varnothing < 12$  mm, however touching should be avoided, and no protection against water.

IP44: Protected against splashed water from all directions and protected against penetration by foreign bodies with  $\varnothing > 1$  mm, however tools and wires should be kept away.

IP Index of Protection: IP 44

impact-resistant and splash-proof: Category 2 (K2) to BGI

Cable class: H07RN-F

Cable structure: 3G1.5

Material cable: Neoprene

Cable length: 25 m

### Technical description

Cable length	25 m
--------------	------

Material cable	Neoprene
suitable for countries	F; B; PL; CZ
Cable structure	3G1.5
Cable class	H07RN-F
Type	25N
impact-resistant and splash-proof	Category 2 (K2) to BGI
IP Index of Protection	IP 44
Power supply	Mains operated
Plug type, input	E
Product name attribute	250 V
AC supply voltage	250 V
Type of product	Extension cable

---

## Accessories

CableFix cable suspension system Type XL	081191 XL
CableFix cable suspension system Type S	081191 S
CableFix cable suspension system Type L	081191 L