




KNUX 160405L Set 10 pieces, Grade: HBX130



Order data

Order number	251092 HBX130
GTIN	4045197664051
Item class	22D

Description

KNUX 160405L Set 10 pieces HBX130 Grade: HBX130

Chip breaker: MG

Chip diverter: 3.2 mm

Cutting depth a_p : 1 - 6 mm

Feed f : 0.2 - 0.7 mm/rev.

Cutting speed v_c main application: 60 - 200 m/min

Technical description

Cutting conditions	slightly interrupted
Chip breaker	MG
Chip diverter	3.2 mm
Corner radius	0.5 mm
Main application	M
Feed f	0.2 - 0.7 mm/rev.
Cutting depth a_p	1 - 6 mm
Grade	HBX130
Cutting speed v_c main application	60 - 200 m/min
Finishing/roughing assignment	Roughing

Tool material	Carbide
Number of changes/inserts	2
ISO code indexable insert	KNUX 160405L
Type of product	Indexable insert for turning