

Garant**Lever lock toolholder, left-hand, Shank / insert size: 32/08mm****Order data**

Order number	251917 32/08
GTIN	4045197674784
Item class	21T

Technical description

suitable indexable insert	WN.. 0804..
Functional width L ₄	40 mm
Shim pins pack	259044 2
Insert size	8 mm
Lever screw	259018 2
Shim punches pack	259047 2
Lever	259015 2
Shim	259031 40
Head length L ₁	23 mm
ISO code toolholder	PWLNR/L 3232 P08
Shank size	32 mm
Overall length L	170 mm
Standard	DIN ISO 5610
Application type	left-hand
Through-coolant	no
Setting angle κ	95 degrees

Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Set of shim pins 10 pieces Type 2	259044 2
Lever Type 2	259015 2
Shim Type 40	259031 40
Lever screw Type 2	259018 2
Shim punches set 10 pieces Type 2	259047 2
Precision Bit for hexagon, 1/4 inch E 6.3 Hexagon 3 mm	674242 3
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500